




Diffuse reflection sensor

OAT-FCKG/T

Article no longer available - archive entry

Alternative articles: OA5209

When selecting an alternative article and accessories please note that technical data may differ!



- 1 selection switch and potentiometer under cover
Receiver in upper lens
transmitter in lower lens

Product characteristics

Type of light	Infrared light
Housing	rectangular

Application

System	Function check output
Function principle	Diffuse reflection sensor

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 50
Protection class		II
Reverse polarity protection		yes
Type of light		Infrared light
Wave length	[nm]	880

Outputs

Electrical design	PNP/NPN
Output function	light-on/dark-on mode; (configurable)
Function check output	yes



Diffuse reflection sensor

OAT-FCKG/T

Max. current load for function check output	[mA]	10
Permanent current rating of switching output DC	[mA]	250
Max. current load in dual output mode	[mA]	100
Switching frequency DC	[Hz]	300
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Time function	[s]	0.5...10

Monitoring range

Range	[mm]	5...1500; (white paper 200 x 200 mm)
Range adjustable		yes
Max. light spot diameter	[mm]	370
Light spot dimensions refer to		at maximum range

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Weight	[g]	0.286
Housing		rectangular
Dimensions	[mm]	90 x 30 x 70
Material		PPO modified
Lens material		PMMA

Displays / operating elements

Display	Switching status	1 x LED, yellow
	Power	1 x LED, green
	Function	1 x LED, red
Operating elements		On-delay or off-delay selectable via slide switch

Accessories

Items supplied	Angle bracket: 1, E20514
	screwdrivers

Remarks

Pack quantity	1 pcs.
---------------	--------



Diffuse reflection sensor

OAT-FCKG/T

Electrical connection

terminals: ...1.5 mm²; Cable sheath: Ø 4.5...10 mm; Cable gland: M16 X 1.5

Connection



5 Function check output

Diagrams and graphs

excess gain graph

