
KQ5100

Capacitive sensor

KQ-3120NFPKG



1 LED
2 sensing face

Product characteristics		
Electrical design		PNP
Output function		normally open / closed; (selectable)
Sensing range	[mm]	12
Communication interface		IO-Link
Housing		rectangular
Dimensions	[mm]	20 x 7 x 48
Electrical data		
Operating voltage	[V]	10...30 DC; (UL - Class 2 source required)
Current consumption	[mA]	< 17
Protection class		III
Reverse polarity protection		yes
Measuring principle		capacitive
Outputs		
Electrical design		PNP
Output function		normally open / closed; (selectable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	10
Short-circuit protection		yes
Overload protection		yes
Monitoring range		
Sensing range	[mm]	12
Real sensing range Sr	[mm]	12 ± 10 %
Accuracy / deviations		
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-20...20

KQ5100

Capacitive sensor

KQ-3120NFPKG

Software / programming			
Parameter setting options		only via IO-Link	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM1 (4,8 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9 CDV	
Profiles		Smart Sensor	
SIO mode		yes	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	371
Operating conditions			
Ambient temperature	[°C]	-40...80	
Protection		IP 65; IP 67	
Tests / approvals			
EMC		EN 61000-4-2	8 kV AD
		EN 61000-4-3	10 V/m
		EN 61000-4-4	2 kV
		EN 61000-4-6	3 V
		EN 55011	class B
Vibration resistance		EN 60068-2-6 Fc	(10...55 Hz) / 1 mm amplitude, vibration duration 5 min., 30 min. per axis with resonance or 55 Hz
Shock resistance		EN 60068-2-27 Ea	30 g 6 shocks / 11 ms half-sine (x, y, z)
MTTF	[years]	771	
Mechanical data			
Weight	[g]	36.7	
Housing		rectangular	
Mounting		non-flush mountable	
Dimensions	[mm]	20 x 7 x 48	
Material		PBT; TPE-U; stainless steel	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
Remarks			
Pack quantity		1 pcs.	

KQ5100


Capacitive sensor

KQ-3120NFPKG

Electrical connection

Cable: 2 m, PUR; 3 x 0.14 mm²

Connection



BK:	OUT / IO-Link
	Core colors :
BK =	black
BN =	brown
BU =	blue