


Fiber-optic amplifier

OBF-FNKG

Article no longer available - archive entry

Alternative articles:

When selecting an alternative article and accessories please note that technical data may differ!



- 1 Mounting on DIN rail
2 setting pushbuttons

Product characteristics

Type of light	red light
Housing	rectangular

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	35; ((24 V))
Protection class	II
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	660

Outputs

Electrical design	NPN
Output function	light-on/dark-on mode; (configurable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	500
Short-circuit protection	yes

OB5020



Fiber-optic amplifier

OBF-FNKG

Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range	
Range [m]	0...1; (Through-beam sensor)
Range [mm]	0...50; (Diffuse reflection sensor)
Range adjustable	yes

Operating conditions	
Ambient temperature [°C]	-25...60
Protection	IP 65

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data	
Housing	rectangular
Dimensions [mm]	36 x 15 x 60
Material	\$3SGLWE



Displays / operating elements		
Display	Switching status	1 x LED, yellow
	Power	1 x LED, green
	Unsafe zone	1 x LED, red

Remarks	
Remarks	light-on mode corresponds to the NC output function for through-beam fibers
	corresponds to the NO output function for diffuse-reflection fibers
	dark-on mode corresponds to the NO output function for through-beam fibers
	corresponds to the NC output function for diffuse-reflection fiber optics
Pack quantity	1 pcs.

Electrical connection

Cable: 2 m, PVC; 3 x 0.34 mm²

Connection



Core colors :
 BN = brown
 BU = blue
 BK = black