




Illuminated capacitive touch sensor

KTMDF-KGRBPKG/0,3M

Article no longer available - archive entry

Alternative articles: KT5111

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	Ø 29 / L = 31

Application

Principle of operation	dynamic
------------------------	---------

Electrical data

Operating voltage [V]	12...30 DC
Current consumption [mA]	30
Protection class	III
Reverse polarity protection	yes
Max. power-on delay time [ms]	500

Outputs

Electrical design	PNP
Output function	normally open
Permanent current rating of switching output DC [mA]	200
Short-circuit protection	yes
Overload protection	yes
Length of output signal [ms]	300

Reaction times

Response time [ms]	35
--------------------	----

KT5109



Illuminated capacitive touch sensor

KTMDF-KGRBPKG/0,3M

Operating conditions

Ambient temperature	[°C]	-40...85
Protection		IP 65; IP 67; IP 69K; (on the front)

Mechanical data

Weight	[g]	43
Dimensions	[mm]	Ø 29 / L = 31
Material		PA 6.6-GF30 black; actuating surface: PA Grilamid TR 90UV

Displays / operating elements

Display	Switching status	1 x LED, red
	Function	1 x LED, green can be triggered

Accessories

Items supplied	lock nuts: 1
	Gasket: 1
Accessories (optional)	Symbol disc


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 0.3 m, PUR

Connection



	Core colors :
BK =	black
BN =	brown
BU =	blue
WH =	white