


LDH100

Oil humidity sensor

OIL HUMIDITY SENSOR



For 8-wire cordsets the core colors are not standardized.
Please note the wiring of the sensor and the cordsets (see data sheet).



Product characteristics

Number of inputs and outputs	Number of analog outputs: 2
Process connection	G 3/4

Application

Media	mineral oils; synthetic esters; biodegradable oils
Tank pressure [bar]	50

Oil

Medium temperature [°C]	-40...105
-------------------------	-----------

Electrical data

Operating voltage [V]	9...33 DC
Current consumption [mA]	< 25
Protection class	III
Reverse polarity protection	no
Measuring principle	capacitive

Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 2
------------------------------	-----------------------------

Outputs

Total number of outputs	2
Number of analog outputs	2
Analog current output [mA]	4...20
Max. load [Ω]	(U _b - 8) x 25
Resolution of analog output	φ: 1% / T: 0.1 K

Measuring/setting range


Temperature monitoring	
Measuring range [°C]	-20...120

LDH100



Oil humidity sensor

OIL HUMIDITY SENSOR

Accuracy / deviations		
Accuracy	φ: ± 3 % / T: ± 2 %	
Reaction times		
Response time	[s]	1.3
Operating conditions		
Ambient temperature	[°C]	-40...85
Storage temperature	[°C]	-40...85
Max. relative air humidity	[%]	100
Protection		IP 67
Tests / approvals		
EMC	EN 13309	
	IEC 61000-6-2	: 2005
	IEC 61000-6-4	: 2006 + AMD1: 2010
Vibration resistance	test following DIN EN 60068-2-6	
MTTF	[years]	90
Mechanical data		
Weight	[g]	176.5
Materials (wetted parts)	aluminum; HNBR; polyurethane resin; epoxy resin	
Process connection	G 3/4	
Remarks		
Remarks	Accuracy values expressed in percent refer to the measuring span	
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M12; coding: A		
		


LDH100



Oil humidity sensor

OIL HUMIDITY SENSOR

Connection



SGND: signal ground
OUT1: oil temperature
OUT2: relative humidity