


Cylinder sensor for tie-rod cylinder

MKZ3000-BPKG/US-100-DPS

Article no longer available - archive entry

Alternative articles: MK5108 + E11799

When selecting an alternative article and accessories please note that technical data may differ!



1 sensing face



Product characteristics

Electrical design	PNP
Output function	normally open
Dimensions [mm]	37.5 x 35 x 35.5

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Reverse polarity protection	yes
Max. power-on delay time [ms]	2

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	300
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Magnetic sensitivity [mT]	3
Travel speed [m/s]	< 5

Accuracy / deviations

Hysteresis [mm]	1
-----------------	---

MK5009



Cylinder sensor for tie-rod cylinder

MKZ3000-BPKG/US-100-DPS

Repeatability	[mm]	0.1
---------------	------	-----

Operating conditions

Ambient temperature	[°C]	-25...75
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)

Mechanical data

Sensing face		centred
Cylinder type		tie rod cylinders
Dimensions	[mm]	37.5 x 35 x 35.5
Material		housing: plastics; Mounting adapter: aluminum

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection - plug

Connector: 1 x M12; coding: A



Connection

