




Through-beam sensor transmitter

OGS-00KG/US100



Product characteristics

Type of light	red light
Housing	Threaded type

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	20
Protection class	II
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	624

Monitoring range

Transmitter / receiver	transmitter
Range [m]	< 25
Range adjustable	no
Max. light spot diameter [mm]	1000
Light spot dimensions refer to	at maximum range

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2
MTTF [years]	629

Mechanical data

Weight [g]	62.3
Housing	Threaded type
Dimensions [mm]	M18 x 1 / L = 72
Thread designation	M18 x 1

OGS500



Through-beam sensor transmitter

OGS-00KG/US100

Material	stainless steel (1.4404 / 316L); PA; EPDM
Lens material	PMMA

Displays / operating elements

Display	Power	1 x LED, green
---------	-------	----------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks


Remarks	cULus - Class 2 source required
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection





Through-beam sensor transmitter

OGS-00KG/US100

Diagrams and graphs

excess gain graph

