


MK5042



T-slot cylinder sensor

MKT3000-ANKG/AS

Article no longer available - archive entry



Product characteristics		
Electrical design		NPN
Output function		normally open
Dimensions	[mm]	14 x 12 x 26
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 10
Reverse polarity protection		yes
Max. power-on delay time	[ms]	2
Outputs		
Electrical design		NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	300
Switching frequency DC	[Hz]	5000
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)

MK5042




T-slot cylinder sensor

MKT3000-ANKG/AS

Overload protection		yes	
Monitoring range			
Magnetic sensitivity	[mT]	2	
Travel speed	[m/s]	< 5	
Accuracy / deviations			
Hysteresis	[mm]	1	
Repeatability	[mm]	0.1	
Operating conditions			
Ambient temperature	[°C]	-25...75	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
Shock/vibration resistance		30 g (11 ms) / 10-55 Hz (1 mm)	
Mechanical data			
Sensing face		front	
Cylinder type		trapezoidal slot cylinders	
Dimensions	[mm]	14 x 12 x 26	
Material		aluminum; plastics	
Displays / operating elements			
Display	Switching status		1 x LED, yellow
Remarks			
Pack quantity		1 pcs.	
Electrical connection - plug			

Connector: 1 x M8; coding: A



Connection

