




Through-beam sensor receiver

OGE-DBOA/LS-100-AK



1 pushbutton



Product characteristics		
Type of light		Infrared light
Housing		Threaded type
Application		
Function principle		Through-beam sensor
Electrical data		
Frequency AC	[Hz]	47...63
Operating voltage	[V]	20...250 AC/DC
Protection class		II
Reverse polarity protection		no
Type of light		Infrared light
Wave length	[nm]	880
Outputs		
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	8
Max. voltage drop switching output AC	[V]	8
Minimum load current	[mA]	5
Max. leakage current	[mA]	1.7
Permanent current rating of switching output AC	[mA]	90; (180 (...40 °C))
Permanent current rating of switching output DC	[mA]	90; (180 (...40 °C))
Short-time current rating of switching output	[mA]	600; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	25
Switching frequency DC	[Hz]	25
Short-circuit proof		no
Overload protection		no



## Through-beam sensor receiver

OGE-DBOA/LS-100-AK

Monitoring range		
Transmitter / receiver		receiver
Range [m]		< 15
Range adjustable		yes
Operating conditions		
Ambient temperature [°C]		-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF [years]		334
Mechanical data		
Weight [g]		38.8
Housing		Threaded type
Dimensions [mm]		M18 x 1 / L = 76
Thread designation		M18 x 1
Material		PBT
Lens material		PMMA
Displays / operating elements		
Display	Switching status	1 x LED, red
	Function	1 x LED, red flashing
Electrical connection		
Required protection		miniature fuse to IEC60127-2 sheet 1; ≤ 2 A; fast acting
Accessories		
Items supplied		lock nuts: 2
Remarks		
Remarks		Recommendation: check the unit for reliable function after a short circuit.
Pack quantity		1 pcs.

## Electrical connection


Connector: 1 x 1/2"; coding: C



## Through-beam sensor receiver

OGE-DBOA/LS-100-AK

## Connection

Note : miniature fuse to IEC60127-2 sheet 1  $\leq 2$  A fast acting

## Diagrams and graphs

excess gain graph

