



Retro-reflective sensor

OGR-DPKG/6M

Article no longer available - archive entry

Alternative articles: OG5086

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available



Product characteristics

Type of light	Infrared light
Housing	Threaded type

Application

Function principle	Retro-reflective sensor
--------------------	-------------------------

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	10; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		Infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	160
Short-circuit protection		yes



Retro-reflective sensor

OGR-DPKG/6M

Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Range	[m]	< 3; (Prismatic reflector Ø 80 E20005)
-------	-----	--

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		Threaded type
Dimensions	[mm]	M18 x 1
Thread designation		M18 x 1
Material		brass nickel-plated
Lens material		glass

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied		lock nuts: 2
----------------	--	--------------


Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Cable: 6 m, PVC; 3 x 0.5 mm²

Connection



	Core colors :
BN =	brown
BU =	blue
BK =	black