


MS5010



Magnetic sensor

MS-3060-BPKG/AS-510-TPS



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	60; (referred to magnet M 4.0)
Housing	rectangular
Dimensions [mm]	28 x 10 x 16

Application

System	gold-plated contacts
--------	----------------------

Electrical data

Operating voltage [V]	10...30 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 10
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

MS5010



Magnetic sensor

MS-3060-BPKG/AS-510-TPS

Monitoring range		
Sensing range	[mm]	60; (referred to magnet M 4.0)
Magnetic sensitivity	[mT]	1.2
Accuracy / deviations		
Hysteresis	[% of Sr]	1...10
Operating conditions		
Ambient temperature	[°C]	-25...75
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5 kV line to line, Ri: 2 Ohm
	EN 61000-4-6 HF conducted	10 V
	EN 55011	class B
MTTF	[years]	2847
Mechanical data		
Weight	[g]	17
Housing		rectangular
Dimensions	[mm]	28 x 10 x 16
Material		housing: PBT orange
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		

Connector: 1 x M8; coding: A; Contacts: gold-plated



MS5010

Magnetic sensor

MS-3060-BPKG/AS-510-TPS



Connection

