




Inductive NAMUR sensor

IFA2002-N/1D/1G



Product characteristics

Electrical design	NAMUR
Output function	normally closed
Sensing range [mm]	2
Housing	Threaded type
Dimensions [mm]	M12 x 1 / L = 30

Electrical data

Connection at circuit amplifier	yes
Switching amplifiers	connection to certified intrinsically safe circuits with the max. values: U = 15 V / I = 50 mA / P = 120 mW
Nominal voltage DC [V]	8.2; (1kΩ)
Supply voltage DC [V]	7.5...30; (when used outside the hazardous area)
Current consumption [mA]	< 1; (disabled; conductive: > 2,1)
Protection class	III

Outputs

Electrical design	NAMUR
Output function	normally closed
Permanent current rating of switching output DC [mA]	30; (when used outside the hazardous area)
Switching frequency DC [Hz]	1200

Monitoring range

Sensing range [mm]	2
Real sensing range Sr [mm]	2 ± 10 %

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-10...10

Operating conditions

Ambient temperature [°C]	-20...80
Note on ambient temperature	when used outside the hazardous area
Protection	IP 67

Tests / approvals

Approval	PTB 01 ATEX 2191; BVS 04 ATEX E153; IECEx BVS 06.0003; TIIS TC16107
----------	---

NF5002



Inductive NAMUR sensor

IFA2002-N/1D/1G

ATEX marking	II 1G Ex ia IIC T6 Ga Ta: -20...70° C
	II 1G Ex ia IIC T5 Ga Ta: -20...80° C
	II 1D Ex ia IIIC T90° C Da Ta: -20...70° C
	II 1D Ex ia IIIC T100° C Da Ta: -20...80° C
EMC	EN 60947-5-6
Shock/vibration resistance	30 g (11 ms) / 10-55 Hz (1 mm)
MTTF [years]	4736

Safety classification

Max. internal capacitance [nF]	140
Max. internal inductance [μH]	340

Mechanical data

Weight [g]	129
Housing	Threaded type
Mounting	flush mountable
Dimensions [mm]	M12 x 1 / L = 30
Thread designation	M12 x 1
Material	brass special coating; sensing face: PC

Accessories

Items supplied	lock nuts: 2
----------------	--------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, PVC; 2 x 0.34 mm²

Connection



BN = Core colors : brown
BU = blue