


Through-beam sensor transmitter

OGSLOOKG/B6/V4A/US-100

Article no longer available - archive entry

Alternative articles: OGS700

When selecting an alternative article and accessories please note that technical data may differ!



1 pushbutton

Product characteristics

Type of light	red light
Laser protection class	2
Housing	Threaded type

Application

System	gold-plated contacts
Function principle	Through-beam sensor

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 17
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	675
Typ. lifetime	[h]	50000

Outputs

Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Transmitter / receiver		transmitter
Range	[m]	< 60
Range adjustable		no
Diameter of the smallest detectable object	[mm]	3
Max. light spot diameter	[mm]	150



Through-beam sensor transmitter

OGSLOOKG/B6/V4A/US-100

Light spot dimensions refer to	at maximum range
--------------------------------	------------------

Operating conditions

Ambient temperature	[°C]	-10...50
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
Laser protection class		2
Notes on laser protection	Caution:	Laser light
	pulse performance:	<= 2,2 mW
	Wave length:	675 nm
	Frequency:	2,2 kHz
	Pulse length:	24 µs
	Do not stare into beam.	
	Avoid exposure to the laser light.	
	laser class:	2
		EN 60825-1

Mechanical data

Housing		Threaded type
Dimensions	[mm]	M18 x 1 / L = 72
Thread designation		M18 x 1
Material		stainless steel (1.4404 / 316L); PBT
Lens material		PMMA

Displays / operating elements

Display	Power	1 x LED, green
---------	-------	----------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



OG5059



Through-beam sensor transmitter

OGSLOOKG/B6/V4A/US-100

Connection

