


## Through-beam sensor receiver

OGELFPKG/V4A/US-100

Article no longer available - archive entry



1 pushbutton

## Product characteristics

Type of light	red light
Housing	Threaded type

## Application

Function principle	Through-beam sensor
--------------------	---------------------

## Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 24
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	675

## Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Max. voltage drop of function check output	[V]	3.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

## Monitoring range

Transmitter / receiver		receiver
Range	[m]	< 6
Range adjustable		yes



Through-beam sensor receiver

OGELFPKG/V4A/US-100

Diameter of the smallest detectable object	[mm]	1
Max. light spot diameter	[mm]	10
Light spot dimensions refer to	at maximum range	

Operating conditions

Ambient temperature	[°C]	-10...50
Protection	IP 67	

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	Threaded type	
Dimensions	[mm]	M18 x 1 / L = 72
Thread designation	M18 x 1	
Material	stainless steel (1.4404 / 316L); PBT	
Lens material	PMMA	

Displays / operating elements

Display	Switching status	1 x LED, yellow
	Power	1 x LED, green

Accessories


Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection

