



Retro-reflective sensor

OGP-FPKG/B1/V4A/6M

Article no longer available - archive entry

Alternative articles: OGP302 or OGP303

When selecting an alternative article and accessories please note that technical data may differ!



1 pushbutton

Product characteristics

Type of light	red light
Housing	Threaded type

Application

System	polarization filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 30
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range

Range	[m]	< 3; (Prismatic reflector Ø 80 E20005)
Range adjustable		yes

OG5106



Retro-reflective sensor

OGP-FPKG/B1/V4A/6M

Max. light spot diameter	[mm]	262
Light spot dimensions refer to		at maximum range
Polarization filter available		yes

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 68; IP 69K

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		Threaded type
Dimensions	[mm]	M18 x 1 / L = 63
Thread designation		M18 x 1
Material		stainless steel (1.4404 / 316L); PBT
Lens material		PMMA

Displays / operating elements

Display	Switching status	1 x LED, yellow
	Power	1 x LED, green
	Function	1 x LED, red

Accessories

Items supplied	lock nuts: 2
----------------	--------------



Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 6 m, PVC; 3 x 0.34 mm²

Connection



Core colors :
BN = brown
BU = blue
BK = black

**Retro-reflective sensor**

OGP-FPKG/B1/V4A/6M

Diagrams and graphs

excess gain graph

