


OGP-FPKG/B1/V4A/US-100

Alternative articles: OGP300 or OGP301

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Type of light	red light
Housing	Threaded type

System	gold-plated contacts; polarization filter; Function check output
Function principle	Retro-reflective sensor

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 32
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Electrical design		PNP
Output function		light-on/dark-on mode; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Function check output		yes
Max. voltage drop of function check output	[V]	3.5
Max. current load for function check output	[mA]	10
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)



Retro-reflective sensor

OGP-FPKG/B1/V4A/US-100

Overload protection	yes
---------------------	-----

Monitoring range

Range [m]	< 3; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes
Max. light spot diameter [mm]	262
Light spot dimensions refer to	at maximum range
Polarization filter available	yes

Operating conditions

Ambient temperature [°C]	-25...80
Protection	IP 68; IP 69K

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	Threaded type
Dimensions [mm]	M18 x 1 / L = 70.5
Thread designation	M18 x 1
Material	stainless steel (1.4404 / 316L); PBT
Lens material	PMMA

Displays / operating elements

Display	Switching status	1 x LED, yellow
	Power	1 x LED, green
	Function	1 x LED, red

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection


Connector: 1 x M12; coding: A; Contacts: gold-plated



Retro-reflective sensor

OGP-FPKG/B1/V4A/US-100

Connection



2 Function check output

Diagrams and graphs

excess gain graph

