


# O2D926



## External illumination

BAR LIGHT 10x150 W/O,3M/US



1 LED



Product characteristics		
Type of light		White light
Application		
Illuminated field	[mm]	10 x 150
Design		bar
Type of operation		high light intensity (pulsed, permanent operation with cooling only); normal light intensity (permanent operation possible)
Electrical data		
Operating voltage	[V]	24 DC
Current consumption	[mA]	Operating mode "permanent operation": 265; operating mode "high light intensity": 475
Type of light		White light

# O2D926



## External illumination

BAR LIGHT 10x150 W/0,3M/US

Color temperature	[K]	5600
-------------------	-----	------

### Inputs

Trigger	24 V PNP
---------	----------

### Operating conditions

Ambient temperature	[°C]	-10...55
Storage temperature	[°C]	-25...75
Protection		IP 65
Overheat protection		yes; (deactivation at 65...75 °C)

### Tests / approvals

Photobiological safety	exempt group; (DIN EN 62471:2008)
------------------------	-----------------------------------

### Mechanical data

Weight	[g]	220.5
Dimensions	[mm]	200 x 13 x 18
Material		aluminum black anodized
Lens material		glass

### Displays / operating elements

Display	Illumination status	1 x LED, yellow
	Power	1 x LED, green
	Excess temperature	1 x LED, red

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

Cable: 0.3 m, PUR, black; 4 x 0.34 mm<sup>2</sup>

Connector: 1 x M12; coding: A




# O2D926



## External illumination

BAR LIGHT 10x150 W/0,3M/US

### Connection



4 Trigger  
2 operating mode "high light intensity"