




Retro-reflective sensor

OIP-FNKG

Article no longer available - archive entry



Product characteristics

Type of light	red light
Housing	Threaded type

Application

System	polarization filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...55 DC
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs


Electrical design		NPN
Output function		light-on/dark-on mode; (programmable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	65
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes



Retro-reflective sensor

OIP-FNKG

Monitoring range		
Range referred to prismatic reflector	[m]	0.15...2; (Prismatic reflector Ø 80 E20005)
Range adjustable		yes
Max. light spot diameter	[mm]	200
Light spot dimensions refer to		at maximum range
Polarization filter available		yes
Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Weight	[g]	0.124
Housing		Threaded type
Dimensions	[mm]	M30 x 1.5 / L = 125
Thread designation		M30 x 1.5
Material		PBT; PPO modified
Lens material		PMMA
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied	lock nuts: 2	
	screwdrivers	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
terminals: ...1.5 mm²; Cable sheath: Ø 7...13 mm; Cable gland: M20 X 1.5		
Connection		



**Retro-reflective sensor**

OIP-FNKG

Diagrams and graphs

excess gain graph

