

OJR200




Retro-reflective LASER sensor

OJR-DPKG/SO/AS

Article to be discontinued

Alternative articles: O6P202
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Function principle		Retro-reflective sensor
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	< 20
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Outputs		
Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5

OJR200



Retro-reflective LASER sensor

OJR-DPKG/SO/AS

Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range	
Range referred to prismatic reflector [m]	1.8; (Prismatic reflector Ø 80 E20005)
Range adjustable	no
Max. light spot diameter [mm]	64
Light spot dimensions refer to	at maximum range

Operating conditions	
Ambient temperature [°C]	-25...60
Protection	IP 67

Tests / approvals	
EMC	EN 60947-5-2
MTTF [years]	905

Mechanical data	
Weight [g]	15.5
Housing	rectangular
Dimensions [mm]	35 x 11 x 24
Material	ABS; SEPS
Lens material	PMMA
Lens alignment	Side sensing

Displays / operating elements	
Display	Switching status 1 x LED, yellow

Remarks	
Remarks	cULus - Class 2 source required
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M8; coding: A





Retro-reflective LASER sensor

OJR-DPKG/SO/AS

Connection

