




Through-beam sensor transmitter

OLS-00KG/US-100

Article no longer available - archive entry

Alternative articles: O5S500 + E21122

When selecting an alternative article and accessories please note that technical data may differ!



1 Pushbutton without function

Product characteristics

Type of light	Infrared light
Housing	rectangular

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 22
Protection class		II
Reverse polarity protection		yes
Overvoltage protection		yes
Type of light		Infrared light
Wave length	[nm]	880

Outputs

Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)

Monitoring range

Transmitter / receiver		transmitter
Range	[m]	< 25
Range adjustable		no
Max. light spot diameter	[mm]	2500

OL5013



Through-beam sensor transmitter

OLS-00KG/US-100

Light spot dimensions refer to _____ at maximum range

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		rectangular
Dimensions	[mm]	75 x 27 x 62
Material		PA; PBT
Lens material		PMMA

Displays / operating elements

Display	Power	1 x LED, green
---------	-------	----------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection

