

OPL-FNKG/IO-LINK/AS

- 1 potentiometer sensitivity
2 output function switch





Photoelectric angle sensor

OPL-FNKG/IO-LINK/AS


Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor: Device Identification; Device Diagnosis; Teach Channel; Switching Channel; Process Data Variable	
SIO mode	yes	
Required master port class	A	
Min. process cycle time [ms]	3.2	
Supported DeviceIDs	Type of operation	DeviceID
	default	1103
Operating conditions		
Ambient temperature [°C]	-25...60	
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
MTTF [years]	709	
Mechanical data		
Weight [g]	116	
Dimensions [mm]	75 x 10 x 75	
Side length X [mm]	50	
Side length Y [mm]	50	
Sensor width Z [mm]	60	
Material	housing: diecast zinc black anodized; lens: glass	
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Remarks		
Remarks	cULus - Class 2 source required	
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M8; coding: A		
		



Photoelectric angle sensor

OPL-FNKG/IO-LINK/AS

Connection



4

OUT / IO-Link