


OPU200



Photoelectric fork sensor

OPU-FCKG/IO-LINK/AS



Product characteristics	
Type of light	Infrared light
Electrical data	
Operating voltage [V]	10...30 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 30
Protection class	III
Reverse polarity protection	yes
Type of light	Infrared light
Wave length [nm]	860
Outputs	
Electrical design	PNP/NPN; (Automatic load detection PNP/NPN)
Output function	light-on/dark-on mode; (selectable)
Max. voltage drop switching output DC [V]	1.5
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	10000
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes
Monitoring range	
Diameter of the smallest detectable object [mm]	0.2
Interfaces	
Communication interface	IO-Link

OPU200



Photoelectric fork sensor

OPU-FCKG/IO-LINK/AS

Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor - SSP 0	Generic Profiled Sensor
	Function	Device identification
	Function	Multiple switching signal
	Function	Process data variable
	Function	Device diagnosis
	Function	Teach channel
SIO mode	yes	
Required master port class	A	
Min. process cycle time [ms]	3.2	
Supported DeviceIDs	Type of operation	DeviceID
	default	1089

Operating conditions

Ambient temperature [°C]	-25...60	
Protection	IP 67	

Tests / approvals

EMC	EN 60947-5-2	
MTTF [years]	744	

Mechanical data

Weight [g]	56	
Dimensions [mm]	25 x 10 x 45	
Fork depth D [mm]	17	
Fork width W [mm]	10	
Material	housing: diecast zinc black anodized; lens: glass	

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Remarks

Remarks	cULus - Class 2 source required	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M8; coding: A; Contacts: 3





Photoelectric fork sensor

OPU-FCKG/IO-LINK/AS

Connection



4 OUT / IO-Link

Other data

operating mode adjustable via IO-Link

	standard	High Resolution	Power	Speed
Resolution	0.2 mm	0.1 mm	1.0 mm	0.2 mm
Repeatability	0.02 mm	0.02 mm	0.02 mm	0.02 mm
Switching frequency	10000 Hz	5000 Hz	250 Hz	14000 Hz
Repeatability	3 σ			