


Retro-reflective sensor

OSP-FNKG/T

Article no longer available - archive entry



- 1 potentiometer timer
2 potentiometer sensitivity
Receiver in upper lens
transmitter in lower lens

Product characteristics

Type of light	red light
Housing	rectangular

Application

System	polarization filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	25; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		NPN
Output function		light-on/dark-on mode; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	40
Short-circuit protection		yes



Retro-reflective sensor

OSP-FNKG/T

Type of short-circuit protection	yes (non-latching)
Overload protection	yes
Time function [s]	0.01...5

Monitoring range

Range [m]	< 6; (Prismatic reflector Ø 80 E20005)
Range adjustable	yes
Polarization filter available	yes

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 65

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	rectangular
Dimensions [mm]	80 x 28 x 95
Material	PPO modified
Lens material	glass

Displays / operating elements

Display	Switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	Angle bracket
	screwdrivers

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

terminals: ...1.5 mm²

Connection

