OT5014


Retro-reflective sensor

OTR-FNKG/US-100-INF

Article no longer available - archive entry

Alternative articles: O5P502

When selecting an alternative article and accessories please note that technical data may differ!



Receiver in lower lens
Transmitter in upper lens

Product characteristics		
Type of light		Infrared light
Housing		rectangular
Application		
Function principle		Retro-reflective sensor
Electrical data		
Operating voltage	[V]	10...50 DC
Current consumption	[mA]	40; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		Infrared light
Wave length	[nm]	880
Outputs		
Electrical design		NPN
Output function		light-on/dark-on mode; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	150

OT5014

Retro-reflective sensor

OTR-FNKG/US-100-INF

Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Monitoring range			
Range	[m]	0.15...5; (Prismatic reflector Ø 80 E20005)	
Range adjustable		yes	
Max. light spot diameter	[mm]	262	
Light spot dimensions refer to		at maximum range	
Operating conditions			
Ambient temperature	[°C]	-25...60	
Protection		IP 65	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
Mechanical data			
Weight	[g]	0.162	
Housing		rectangular	
Dimensions	[mm]	75 x 19 x 30	
Material		PBT	
Lens material		PMMA	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
		Power	1 x LED, green
Accessories			
Items supplied		Angle bracket: 1, E20461	
		screwdrivers	
Remarks			
Pack quantity		1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A



OT5014

Retro-reflective sensor

OTR-FNKG/US-100-INF

Connection



Diagrams and graphs

excess gain graph

