


Retro-reflective sensor

OTR-FPKG/24V/US-100-IPF

Article no longer available - archive entry

Alternative articles: OT5013

When selecting an alternative article and accessories please note that technical data may differ!



Receiver in lower lens
Transmitter in upper lens

Product characteristics

Type of light	Infrared light
Housing	rectangular

Application

Function principle	Retro-reflective sensor
--------------------	-------------------------

Electrical data

Operating voltage	[V]	18...36 DC
Current consumption	[mA]	40; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		Infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	100

**Retro-reflective sensor**

OTR-FPKG/24V/US-100-IPF

Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Range	[m]	0.15...5; (Prismatic reflector Ø 80 E20005)
Range adjustable		yes
Wave length range	[µm]	< 7

Operating conditions

Ambient temperature	[°C]	-10...50
Protection		IP 65

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		rectangular
Dimensions	[mm]	75 x 19 x 30
Material		PBT
Lens material		PMMA

Displays / operating elements

Display	Switching status	1 x LED, yellow
	Power	1 x LED, green

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A





Retro-reflective sensor

OTR-FPKG/24V/US-100-IPF

Connection

