OU5071

Diffuse reflection sensor

OUN-HPKG/6M

Article no longer available - archive entry

Alternative articles: OU5069

When selecting an alternative article and accessories please note that technical data may differ!



Receiver in upper lens
transmitter in lower lens

Product characteristics		
Type of light		Infrared light
Housing		rectangular
Application		
System		short ranges
Function principle		Diffuse reflection sensor
Electrical data		
Operating voltage	[V]	10...55 DC
Current consumption	[mA]	35; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		Infrared light
Wave length	[nm]	880
Outputs		
Electrical design		PNP
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	160
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Monitoring range		
Range	[mm]	20...40; (white paper 200 x 200 mm)

OU5071

Diffuse reflection sensor

OUN-HPKG/6M

Max. light spot diameter	[mm]	20	
Light spot dimensions refer to		at maximum range	
Short ranges		yes	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
Mechanical data			
Weight	[g]	295	
Housing		rectangular	
Dimensions	[mm]	28 x 16 x 51	
Material		PPO modified	
Lens material		glass	
Displays / operating elements			
Display		Switching status	1 x LED, yellow
Accessories			
Items supplied		Angle bracket: 1, E20211	
Remarks			
Pack quantity		1 pcs.	
Electrical connection			

Cable: 6 m, PVC; 3 x 0.34 mm²

Connection



	Core colors :
BN =	brown
BU =	blue
BK =	black

OU5071

Diffuse reflection sensor

OUN-HPKG/6M

Diagrams and graphs

excess gain graph