




Infrared temperature sensor

OWL-3506-ABOA

Article no longer available - archive entry

Alternative articles: TW7001 + E35065

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Housing	tubular
---------	---------

Electrical data

Operating voltage	[V]	20...250 AC/DC
Reverse polarity protection		no

Outputs

Max. voltage drop switching output DC	[V]	10.5
Max. voltage drop switching output AC	[V]	10.5
Minimum load current	[mA]	15
Max. leakage current	[mA]	7
Permanent current rating of switching output AC	[mA]	200; (250 (...50 °C))
Permanent current rating of switching output DC	[mA]	50
Short-time current rating of switching output	[mA]	1500; (10 ms / 0,5 Hz)
Switching frequency AC	[Hz]	20
Switching frequency DC	[Hz]	25
Short-circuit proof		no
Overload protection		no

Monitoring range

Detection range hysteresis	[%]	1...15
----------------------------	-----	--------



Infrared temperature sensor


OWL-3506-ABOA

Operating conditions		
Ambient temperature	[°C]	-20...60
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		tubular
Dimensions	[mm]	Ø 58 / L = 200
Material		housing: brass white bronze coated
Lens material		glass
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Remarks		
Remarks	Recommendation: check the unit for reliable function after a short circuit.	
Pack quantity	1 pcs.	
Electrical connection		

Connector: 1 x 7/8"



Connection



Note : miniature fuse to IEC60127-2 sheet 1 ≤ 2 A fast acting