


## Through-beam sensor receiver

OFE-FPKG/4M

Article no longer available - archive entry



## Product characteristics

Housing	Threaded type
---------	---------------

## Application

Function principle	Through-beam sensor
--------------------	---------------------

## Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 25
Protection class		II
Reverse polarity protection		yes

## Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	400
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

## Monitoring range

Transmitter / receiver		receiver
Range	[m]	< 4

## Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 67

## Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

## Mechanical data

Housing		Threaded type
Dimensions	[mm]	M12 x 1 / L = 60
Thread designation		M12 x 1



OF5069



Through-beam sensor receiver

OFE-FPKG/4M

Material	brass nickel-plated	
Lens material	PMMA	
Displays / operating elements		
Display	Switching status	1 x LED, yellow
	Power	1 x LED, green
Accessories		
Items supplied	lock nuts: 2	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 4 m, PUR; 3 x 0.34 mm²		
Connection		



BN = Core colors :  
BU = brown  
BK = blue  
BK = black



## Through-beam sensor receiver

OFE-FPKG/4M

### Diagrams and graphs

excess gain graph

