




Through-beam sensor receiver

OGE-FPKG/US-100

Article no longer available - archive entry



1 pushbutton

Product characteristics

Housing	Threaded type
---------	---------------

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	< 24
Protection class		II
Reverse polarity protection		yes

Outputs

Electrical design	PNP	
Output function	light-on/dark-on mode; (configurable)	
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range

Transmitter / receiver		receiver
Range	[m]	< 15
Range adjustable		yes

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2
-----	--------------



Through-beam sensor receiver

OGE-FPKG/US-100

Mechanical data	
Housing	Threaded type
Dimensions [mm]	M18 x 1 / L = 72
Thread designation	M18 x 1
Material	PC
Lens material	PMMA


Displays / operating elements		
Display	Switching status	1 x LED, yellow
	Power	1 x LED, green

Accessories	
Items supplied	lock nuts: 2


Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection





Through-beam sensor receiver

OGE-FPKG/US-100

Diagrams and graphs

excess gain graph

