


PE3226



Pressure sensor with display

PE-003PRBN14-KFPKG/US/ /E

Article no longer available - archive entry



- 1 7-segment LED display
- 2 Programming button



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1
Measuring range [psi]	0...30
Process connection	threaded connection 1/4" NPT external thread

Application

Application	for industrial applications
Media	liquids and gases
Cannot be used for	oils
Medium temperature [°C]	-25...80
Min. bursting pressure [psi]	725
Pressure rating [psi]	290
Type of pressure	relative pressure

Electrical data

Operating voltage [V]	20...30 DC
Current consumption [mA]	< 60
Reverse polarity protection	yes
Power-on delay time [s]	0.2
Integrated watchdog	yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1
------------------------------	---



Pressure sensor with display

PE-003PRBN14-KFPKG/US/ /E

Outputs											
Total number of outputs	2										
Output signal	switching signal; analog signal; (configurable)										
Electrical design	PNP										
Number of digital outputs	1										
Max. voltage drop switching output DC [V]	2										
Permanent current rating of switching output DC [mA]	250										
Number of analog outputs	1										
Analog current output [mA]	4...20										
Max. load [Ω]	500										
Short-circuit protection	yes										
Type of short-circuit protection	yes (non-latching)										
Overload protection	yes										
Measuring/setting range											
Measuring range [psi]	0...30										
Set point SP [psi]	0.3...30										
Reset point rP [psi]	0.1...29.8										
In steps of [psi]	0.2										
Accuracy / deviations											
Switch point accuracy [% of the final value]	< ± 1,5										
Repeatability [% of the final value]	< ± 0,25; (with temperature fluctuations < 10 K)										
Characteristics deviation [% of the final value]	< ± 1,0										
Temperature drift per 10 K	< ± 0.3										
Reaction times											
Switching frequency for a given set response time of one output	Response time (dAP) [ms]	3	6	10	17	30	60	125	250	500	
	Switching frequency [Hz]	170	80	50	30	16	8	4	2	1	
Response time [ms]	at rectangular pressure characteristic; Set point (SPx) = 70 %; Reset point (rPx) = 30 %										
Delay time programmable dS, dr [s]	0, 0,2,...10, 11,...50										
Max. response time analog output [ms]	3										
Software / programming											
Adjustment of the switch point	Programming button										
Operating conditions											
Ambient temperature [°C]	-25...80										
Storage temperature [°C]	-40...100										
Protection	IP 65										

PE3226



Pressure sensor with display

PE-003PRBN14-KFPKG/US/ /E

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

Mechanical data	
Material	EPDM/X; FKM; NBR; PBT; PC; PTFE; stainless steel (1.4301 / 304)
Materials (wetted parts)	EPDM/X; ceramics; stainless steel (1.4305 / 303)
Min. pressure cycles	100 million
Process connection	threaded connection 1/4" NPT external thread

Displays / operating elements		
Display	Switching status	LED, red
	Function display	7-segment LED display
	Measured values	7-segment LED display

Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection

