




LASER diffuse reflection sensor

OJHLFPKG/SO/AS



- 1 pushbutton
Receiver in upper lens
transmitter in lower lens



Product characteristics		
Type of light		red light
Laser protection class		1
Housing		rectangular
Application		
System		Background suppression
Function principle		Diffuse reflection sensor
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	13
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	650
Typ. lifetime	[h]	50000
Outputs		
Electrical design		PNP



LASER diffuse reflection sensor

OJHLFPKG/SO/AS

Output function	light-on/dark-on mode; (programmable)	
Max. voltage drop switching output DC [V]	2.5	
Permanent current rating of switching output DC [mA]	200	
Switching frequency DC [Hz]	1000	
Short-circuit protection	yes	
Type of short-circuit protection	yes (non-latching)	
Overload protection	yes	
Monitoring range		
Range [mm]	7...150; (white paper 200 x 200 mm 90 % remission)	
Range adjustable	yes	
Diameter of the smallest detectable object [mm]	0.8	
Max. light spot diameter [mm]	0.8	
Background suppression available	yes	
Operating conditions		
Ambient temperature [°C]	-10...60	
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
Laser protection class	1	
Notes on laser protection	Caution:	Laser light
	laser class:	1
		EN / IEC60825-1:2007
		EN / IEC60825-1:2014
		Complies with 21 CFR 1040 except for deviations pursuant to Laser Notice No. 50, dated June 2007.
MTTF [years]	501	
Mechanical data		
Weight [g]	28.25	
Housing	rectangular	
Dimensions [mm]	35 x 11 x 24	
Material	housing: ABS; LED window: SEPS; pushbutton: SEPS	
Lens material	PMMA	
Lens alignment	Side sensing	
Displays / operating elements		
Display	Switching status	1 x LED, yellow
	Power	1 x LED, green
Electronic lock	yes	
Accessories		
Items supplied	screws: 2	
	spring washers: 2	
	Nuts: 2	




LASER diffuse reflection sensor

OJHLFPKG/SO/AS


Remarks	
Remarks	cULus - Class 2 source required
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M8; coding: A




Connection



2 Teach

Diagrams and graphs




- a: sensor
- b: object
- c: background
- x: distance sensor/object [mm]
- y: min. distance object/background [mm]



LASER diffuse reflection sensor

OJHLFPKG/SO/AS

Background suppression chart



x: distance sensor/object [mm]

y: min. distance object/background [mm]

1 = object black (6 % remission) , Background white (90 % remission)

2 = object grey (18 % remission) , Background white (90 % remission)

3 = object white (90 % remission) , Background white (90 % remission)