

OK5004

Fiber-optic amplifier


OKF-FPKG/10M



Article no longer available - archive entry

Alternative articles: OK5008

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Type of light	red light
Housing	rectangular

Electrical data

Operating voltage [V]	10...50 DC
Current consumption [mA]	< 30; ((24 V))
Protection class	III
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	660

Outputs

Electrical design	PNP
Output function	light-on/dark-on mode; (programmable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	120
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Monitoring range

Range [m]	0...0.12; (Through-beam sensor)
Range [mm]	0...40; (Diffuse reflection sensor)
Range adjustable	yes



OK5004



Fiber-optic amplifier

OKF-FPKG/10M

Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 65
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	529
Mechanical data		
Housing		rectangular
Dimensions	[mm]	50 x 19 x 35
Material		PPO modified
Lens alignment		Side sensing
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied	screwdrivers	
	screws: 2 x M4 x 25	
	washers: 2	
	spring washers: 2	
	Nuts: 2	
Remarks		
Remarks	light-on mode corresponds to the NC output function for through-beam fibers	
	corresponds to the NO output function for diffuse-reflection fibers	
	dark-on mode corresponds to the NO output function for through-beam fibers	
	corresponds to the NC output function for diffuse-reflection fiber optics	
Pack quantity	1 pcs.	
Electrical connection		
Cable: 10 m, PVC; 4 x 0.34 mm²		
Connection		



Core colors :
BN = brown
BU = blue
BK = black
WH = white