


Flush pressure sensor with analog display

PG-1-1BREA01-MFRKG/US /P



- 1 analog display
 2 alphanumeric display 4-digit
 3 Touch pad (programming button)

ACS CRN EC 1935/2004 EHEDG Certified FCM Reg31 UK

Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1		
Measuring range	-1...1 bar	-1000...1000 mbar	-14.5...14.5 psi
Process connection	threaded connection G 1 external thread Aseptoflex Vario		
Application			
System	gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Media	viscous media and liquids with suspended particles; liquids and gases		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	30 bar	435 psi	
Pressure rating	10 bar	145 psi	
Type of pressure	relative pressure; vacuum		
No dead space	yes		
MAWP (for applications according to CRN) [bar]	10		

Flush pressure sensor with analog display

PG-1-1BREA01-MFRKG/US /P

Electrical data			
Operating voltage	[V]	18...32 DC	
Current consumption	[mA]	< 70; (24 V)	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Protection class		III	
Reverse polarity protection		yes	
Power-on delay time	[s]	6	
Measuring principle		hydrostatic	
Integrated watchdog		yes	
Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 1; Number of analog outputs: 1	
Outputs			
Total number of outputs		2	
Output signal		switching signal; analog signal; (configurable)	
Electrical design		PNP/NPN	
Number of digital outputs		1	
Output function		normally open / closed; (configurable)	
Max. voltage drop switching output DC	[V]	2	
Permanent current rating of switching output DC	[mA]	250	
Switching frequency DC	[Hz]	50	
Number of analog outputs		1	
Analog current output	[mA]	4...20, invertible; (scalable)	
Max. load	[Ω]	(Ub - 10 V) / 20 mA	
Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Measuring/setting range			
Measuring range	-1...1 bar	-1000...1000 mbar	-14.5...14.5 psi
Set point SP	-0.998...1.6 bar		-14.48...23.2 psi
Reset point rP	-1...1.598 bar		-14.5...23.18 psi
Analog start point	-1...1.1 bar		-14.5...15.96 psi
Analog end point	-0.5...1.6 bar		-7.26...23.2 psi
In steps of	0.001 bar		0.02 psi
Accuracy / deviations			
Switch point accuracy	$\pm 0,2$; (Turn down 1:1)		
Repeatability	[% of the span]	$\pm 0,1$; (with temperature fluctuations < 10 K; Turn down 1:1)	
Characteristics deviation	$\pm 0,2$; (Turn down 1:1, linearity, incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1)		
Linearity deviation	[% of the span]	$\pm 0,15$; (Turn down 1:1)	
Hysteresis deviation	[% of the span]	$\pm 0,15$; (Turn down 1:1)	

PG2799



Flush pressure sensor with analog display

PG-1-1BREA01-MFRKG/US / IP

Long-term stability [% of the span]		
		< ± 0,1; (Turn down 1:1; per year)
Temperature coefficient zero point [% of the span / 10 K]		
		< ± 0,05; (0...70 °C)
Temperature coefficient span [% of the span / 10 K]		
		< ± 0,15; (0...70 °C)
Reaction times		
Response time	[ms]	< 10
Damping process value dAP	[s]	0.01...30
Damping for the analog output dAA	[s]	0.01...30
Step response time analog output	[ms]	25
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]	100
Note on approval	Factory certificate available as download at www.factory-certificate.ifm	
Mechanical data		
Weight	[g]	518.75
Material	stainless steel (1.4404 / 316L); PA; FKM; PTFE; viewing glass: laminated safety glass 4 mm	
Materials (wetted parts)	ceramics (99.9 % Al2O3); stainless steel (1.4435 / 316L); surface characteristics: Ra < 0,4 / Rz 4; PTFE	
Min. pressure cycles	100 million	
Process connection	threaded connection G 1 external thread Aseptoflex Vario	
Displays / operating elements		
Display	Display unit	2 x LED, green
	Switching status	LED, yellow
	Switch points	LED ring, red
	Function display	alphanumeric display, red 4-digit
	Measured values	analog display, 0...350° rotatable, pointer not visible when unit disconnected
	Measured values	alphanumeric display, red 4-digit
With scale	yes	
Extended display range (max.)	1.6 bar	23.2 psi

Flush pressure sensor with analog display

PG-1-1BREA01-MFRKG/US /P

Remarks

Remarks

characteristics deviation in the extended display range: 1.5 % of the span

Pack quantity



1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

OUT1
OUT2Switching output
analog output