

PI2652




Flush pressure sensor with display

PI-100-SEA01-MFRKG/US/ /P

Article no longer available - archive entry

Alternative articles: PI2692

When selecting an alternative article and accessories please note that technical data may differ!



- 1 7-segment LED display
2 Programming button



Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1		
Measuring range	-1...100 bar	-10...1450 psi	-0.1...10 MPa
Process connection	threaded connection G 1 external thread		

Application

System	gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Installation	Freely rotatable housing 350°		
Media	viscous media and liquids with suspended particles; liquids and gases		
Conditionally suitable for	For gaseous media the application is limited to max. 25 bar.		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	650 bar	9425 psi	65 MPa
Pressure rating	200 bar	2900 psi	20 MPa
Type of pressure	relative pressure		



Flush pressure sensor with display

PI-100-SEA01-MFRKG/US/ /P

No dead space	yes
---------------	-----

Electrical data

Operating voltage [V]	20...30 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 60
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	0.2
Integrated watchdog	yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1
------------------------------	---

Outputs

Total number of outputs	2
Output signal	switching signal; analog signal; (configurable)
Electrical design	PNP/NPN
Number of digital outputs	2
Output function	normally open / closed; (configurable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	< 170
Number of analog outputs	1
Analog current output [mA]	4...20; (scalable 1:4)
Max. load [Ω]	(U _b - 10 V) / 20 mA
Analog voltage output [V]	0...10; (scalable 1:4)
Min. load resistance [Ω]	2000
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes

Measuring/setting range

Measuring range	-1...100 bar	-10...1450 psi	-0.1...10 MPa
Set point SP	0...100 bar	0...1450 psi	0...10 MPa
Reset point rP	-0.5...99.5 bar	-10...1440 psi	-0.05...9.95 MPa
Analog start point	-1...75 bar	-10...1090 psi	-0.1...7.5 MPa
Analog end point	24...100 bar	350...1450 psi	2.4...10 MPa
In steps of	0.1 bar	10 psi	0.01 MPa

Accuracy / deviations

Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)
Characteristics deviation [% of the span]	< ± 0,6; (Turn down 1:1, linearity, incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1)
Linearity deviation [% of the span]	< ± 0,5; (Turn down 1:1)
Hysteresis deviation	< ± 0,1; (Turn down 1:1)



Flush pressure sensor with display

PI-100-SEA01-MFRKG/US/ /P

	[% of the span]	
Long-term stability		$< \pm 0,1$; (Turn down 1:1; per year)
	[% of the span]	
Temperature coefficient zero point		$< \pm 0,1$; (0...80 °C)
	[% of the span / 10 K]	
Temperature coefficient span		$< \pm 0,2$; (0...80 °C)
	[% of the span / 10 K]	

Reaction times		
Response time	[ms]	< 3
Damping process value dAP	[s]	0...4
Damping for the analog output dAA in steps	[s]	0 - 0,1 - 0,5 - 2
Max. response time analog output	[ms]	3

Software / programming		
Parameter setting options		hysteresis / window; normally open / closed; switching logic; current/ voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; Zero point; span

Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

Mechanical data		
Material		stainless steel (1.4404 / 316L); PBT; PC; PEI; EPDM/X; FKM
Materials (wetted parts)		stainless steel (1.4404 / 316L); ceramics; PTFE
Min. pressure cycles		100 million
Process connection		threaded connection G 1 external thread

Displays / operating elements		
Display	Switching status	2 x LED, red
	Function display	7-segment LED display
	Measured values	7-segment LED display
Display unit		bar; psi; MPa

Remarks		
Remarks		The 3-A qualification is only valid if adapters with 3-A qualification are used for installation.
Pack quantity		1 pcs.



Flush pressure sensor with display





PI-100-SEA01-MFRKG/US/ /P

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1
OUT2

Switching output
Switching output
analog output