




Flush pressure sensor with display

PI-010-RES30-MFRKG/US/ /P

Article to be discontinued
Discontinuation date: 03/31/2024

Alternative articles: PI1004 or PI1704
When selecting an alternative article and accessories please note that technical data may differ!

Please do not use for new projects.
no more adapters available as accessories



- 1 alphanumeric display 4-digit
- 2 status LEDs
- 3 Programming button
- 4 Aseptoflex sealing edge
- 5 Aseptoflex thread



Product characteristics			
Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1		
Measuring range	-1...10 bar	-14.5...145 psi	-0.1...1 MPa
Process connection	threaded connection Aseptoflex external thread Aseptoflex		
Application			
System	gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Installation	Freely rotatable housing 350°		
Media	viscous media and liquids with suspended particles; liquids and gases		



Flush pressure sensor with display

PI-010-RES30-MFRKG/US/ /P

Medium temperature	[°C]	-25...125; (145 max. 1h)		
Min. bursting pressure		150 bar	2175 psi	15 MPa
Pressure rating		50 bar	725 psi	5 MPa
Type of pressure		relative pressure		
No dead space		yes		

Electrical data

Operating voltage	[V]	18...32 DC		
Current consumption	[mA]	< 50		
Min. insulation resistance	[MΩ]	100; (500 V DC)		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	0.5		
Integrated watchdog		yes		

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1; Number of analog outputs: 1			
------------------------------	---	--	--	--

Outputs

Total number of outputs		2		
Output signal		switching signal; analog signal; (configurable)		
Electrical design		PNP/NPN		
Number of digital outputs		1		
Output function		normally open / closed; (configurable)		
Max. voltage drop switching output DC	[V]	2		
Permanent current rating of switching output DC	[mA]	250		
Switching frequency DC	[Hz]	6		
Number of analog outputs		1		
Analog current output	[mA]	4...20, invertible; (scalable 1:4)		
Max. load	[Ω]	(U _b - 10 V) / 20 mA		
Analog voltage output	[V]	0...10, invertible; (scalable 1:4)		
Min. load resistance	[Ω]	2000		
Short-circuit protection		yes		
Type of short-circuit protection		yes (non-latching)		
Overload protection		yes		

Measuring/setting range

Measuring range	-1...10 bar	-14.5...145 psi	-0.1...1 MPa
Set point SP	-0.98...10 bar	-14.2...145 psi	-0.098...1 MPa
Reset point rP	-1...9.98 bar	-14.5...144.7 psi	-0.1...0.998 MPa
Analog start point	-1...7.25 bar	-14.5...105.1 psi	-0.1...0.725 MPa
Analog end point	1.75...10 bar	25.4...145 psi	0.175...1 MPa
In steps of	0.01 bar	0.1 psi	0.001 MPa
Factory setting		SP1 = 2.50 bar	rP1 = 2.30 bar
		ASP = 0.00 bar	AEP = 10.00 bar

Accuracy / deviations

Switch point accuracy	< ± 0.2; (Turn down 1:1)			
-----------------------	--------------------------	--	--	--



Flush pressure sensor with display

PI-010-RES30-MFRKG/US/ /P

	[% of the span]	
Repeatability	[% of the span]	$< \pm 0,1$; (with temperature fluctuations < 10 K; Turn down 1:1)
Characteristics deviation	[% of the span]	$< \pm 0,2$; (Turn down 1:1, linearity, incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1)
Linearity deviation	[% of the span]	$< \pm 0,15$; (Turn down 1:1)
Hysteresis deviation	[% of the span]	$< \pm 0,15$; (Turn down 1:1)
Long-term stability	[% of the span]	$< \pm 0,1$; (Turn down 1:1; per year)
Temperature coefficient zero point	[% of the span / 10 K]	$< \pm 0,05$; (0...70 °C)
Temperature coefficient span	[% of the span / 10 K]	$< \pm 0,15$; (0...70 °C)
Reaction times		
Response time	[ms]	< 100
Damping process value dAP	[s]	0.1...100
Damping for the analog output dAA	[s]	0.1...100
Step response time analog output	[ms]	25
Software / programming		
Parameter setting options		hysteresis / window; normally open / closed; switching logic; current/ voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; Zero point; span
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]	173
Mechanical data		
Weight	[g]	411.5
Material		stainless steel (1.4404 / 316L); PC; PBT; PEI; FKM; PTFE
Materials (wetted parts)		ceramics (99.9 % Al ₂ O ₃); stainless steel (1.4435 / 316L); surface characteristics: Ra $< 0,4$ / Rz 4; PTFE
Min. pressure cycles		100 million
Process connection		threaded connection Aseptoflex external thread Aseptoflex

PI2094




Flush pressure sensor with display

PI-010-RES30-MFRKG/US/ /P



Displays / operating elements		
Display	Display unit	4 x LED, green
	Switching status	LED, yellow
	Function display	alphanumeric display, 4-digit
	Measured values	alphanumeric display, 4-digit
Display unit	bar; psi; MPa; % of the span	
Remarks		
Remarks	The 3-A qualification is only valid if adapters with 3-A qualification are used for installation.	
Notes	Please do not use for new projects.; no more adapters available as accessories	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1 Switching output
OUT2 analog output