




Through-beam sensor transmitter

ORS-V/6M

Article no longer available - archive entry



Product characteristics

Type of light	Infrared light
Housing	rectangular

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Connection at circuit amplifier	yes
Switching amplifiers	Connection at circuit amplifier OV5012, OV0010
Type of light	Infrared light
Wave length [nm]	950

Outputs

Short-circuit protection	no
Overload protection	no

Monitoring range

Transmitter / receiver	transmitter
Range [m]	< 2

Operating conditions

Ambient temperature [°C]	-20...80
Protection	IP 67

Tests / approvals

EMC	EN 60947-5-2
-----	--------------

Mechanical data

Housing	rectangular
---------	-------------

OR0018



Through-beam sensor transmitter

ORS-V/6M

Dimensions	[mm]	25 x 10 x 15
Material		PPO modified

Accessories

Items supplied	Angle bracket: 1, E20212
----------------	--------------------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 6 m; 1 x 0.14 mm²

Connection



RD = Core colors :
screen = red
screen