

PI7698




Flush pressure sensor with display

PI-,25BREA01-QFRKG/US/ IP

Article no longer available - archive entry

Alternative articles: PI2898 or PI2798
When selecting an alternative article and accessories please note that technical data may differ!



- 1 alphanumeric display 4-digit
- 2 status LEDs
- 3 Programming button



Product characteristics		
Number of inputs and outputs	Number of digital outputs: 2	
Measuring range	-0.0124...0.25 bar	-12.4...250 mbar
Process connection	threaded connection G 1 external thread sealing cone	
Application		
System	gold-plated contacts	
Application	flush mountable for the food and beverage industry	
Installation	Freely rotatable housing 350°	
Media	viscous media and liquids with suspended particles; liquids and gases	
Medium temperature [°C]	-25...125; (145 max. 1h)	
Min. bursting pressure [mbar]	30000	
Pressure rating [mbar]	6000	
Type of pressure	relative pressure	



Flush pressure sensor with display

PI-25BREA01-QFRKG/US/ IP

No dead space		yes	
Electrical data			
Operating voltage		[V]	18...32 DC
Current consumption		[mA]	< 50
Min. insulation resistance		[MΩ]	100; (500 V DC)
Protection class			III
Reverse polarity protection			yes
Power-on delay time		[s]	0.5
Integrated watchdog			yes
Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 2	
Outputs			
Total number of outputs		2	
Output signal		switching signal	
Electrical design		PNP/NPN	
Number of digital outputs		2	
Output function		normally open / closed; (configurable)	
Max. voltage drop switching output DC		[V]	2
Permanent current rating of switching output DC		[mA]	250
Switching frequency DC		[Hz]	85
Short-circuit protection		yes	
Type of short-circuit protection		yes (non-latching)	
Overload protection		yes	
Measuring/setting range			
Measuring range		-0.0124...0.25 bar	-12.4...250 mbar
Set point SP		[mbar]	-12...250
Reset point rP		[mbar]	-12.4...249.6
In steps of		[mbar]	0.2
Factory setting		SP1 = 62.4 mbar	rP1 = 57.4 mbar
		SP2 = 187.4 mbar	rP2 = 182.4 mbar
Accuracy / deviations			
Switch point accuracy		< ± 0,2; (Turn down 1:1)	
[% of the span]			
Repeatability		< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)	
[% of the span]			
Characteristics deviation		< ± 0,2; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)	
[% of the span]			
Linearity deviation		< ± 0,15; (Turn down 1:1)	
[% of the span]			
Hysteresis deviation		< ± 0,15; (Turn down 1:1)	
[% of the span]			
Long-term stability		< ± 0,1; (Turn down 1:1; per year)	
[% of the span]			

PI7698



Flush pressure sensor with display

PI-,25BREA01-QFRKG/US/ IP

Temperature coefficient zero point [% of the span / 10 K]	< ± 0,05; (0...70 °C)	
Temperature coefficient span [% of the span / 10 K]	< ± 0,15; (0...70 °C)	
Reaction times		
Response time [ms]	< 6	
Damping process value dAP [s]	0...100	
Software / programming		
Parameter setting options	hysteresis / window; normally open / closed; switching logic; current/voltage output; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit; Zero point; span	
Operating conditions		
Ambient temperature [°C]	-25...80	
Storage temperature [°C]	-40...100	
Protection	IP 67; IP 69K	
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Weight [g]	438.4	
Material	stainless steel (1.4404 / 316L); PC; PBT; PEI; FKM; PTFE	
Materials (wetted parts)	ceramics (99.9 % Al2O3); stainless steel (1.4435 / 316L); surface characteristics: Ra < 0,4 / Rz 4; PTFE	
Min. pressure cycles	100 million	
Process connection	threaded connection G 1 external thread sealing cone	
Displays / operating elements		
Display	Display unit	5 x LED, green
	Switching status	2 x LED, yellow
	Measured values	alphanumeric display, 4-digit
	Parameter setting	alphanumeric display, 4-digit
Display unit	mbar; kPa; inH2O; mmWS; % of the span	
Remarks		
Remarks	The 3-A qualification is only valid if adapters with 3-A qualification are used for installation.	
Pack quantity	1 pcs.	

PI7698



Flush pressure sensor with display

PI-,25BREA01-QFRKG/US/ IP

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



OUT1	Switching output Diagnostic output
OUT2	Switching output