


Diffuse reflection sensor

OTT-FPKG/US-100-IPF

Article no longer available - archive entry



Receiver in lower lens
Transmitter in upper lens

Product characteristics

Type of light	Infrared light
Housing	rectangular

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Electrical data

Operating voltage	[V]	10...50 DC
Current consumption	[mA]	40; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		Infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	150
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)

OT5045



Diffuse reflection sensor

OTT-FPKG/US-100-IPF

Overload protection	yes
---------------------	-----

Monitoring range

Range [mm]	10...40; (white paper 200 x 200 mm)
------------	-------------------------------------

Range adjustable	yes
------------------	-----

Operating conditions

Ambient temperature [°C]	-25...60
--------------------------	----------

Protection	IP 65
------------	-------

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing	rectangular
---------	-------------

Dimensions [mm]	75 x 19 x 30
-----------------	--------------

Material	PBT
----------	-----

Lens material	PMMA
---------------	------

Displays / operating elements

Display	Switching status	1 x LED, yellow
	Power	1 x LED, green

Accessories

Items supplied	Angle bracket
	screwdrivers

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



OT5045



Diffuse reflection sensor

OTT-FPKG/US-100-IPF

Connection

