




Flush pressure transmitter

PL-100-SEA01-A-ZVG/US/ /P

Article no longer available - archive entry



1 Tightening torque 20 Nm



Product characteristics

Number of inputs and outputs	Number of analog outputs: 1
Measuring range [bar]	0...100
Process connection	threaded connection G 1 external thread

Application

Application	flush mountable for the food and beverage industry
Media	viscous media and liquids with suspended particles; liquids and gases
Conditionally suitable for	For gaseous media the application is limited to max. 25 bar.
Medium temperature [°C]	-25...80
Min. bursting pressure [bar]	650
Pressure rating [bar]	150
Type of pressure	relative pressure
No dead space	yes

Electrical data

Operating voltage [V]	10.8...30 DC
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes

Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 1
------------------------------	-----------------------------

PL3652



Flush pressure transmitter

PL-100-SEA01-A-ZVG/US/ /P

Outputs		
Total number of outputs		1
Output signal		analog signal
Number of analog outputs		1
Analog current output	[mA]	4...20
Max. load	[Ω]	660; (U _b = 24 V; (U _b - 10,8 V) / 20 mA)
Overload protection		yes
Measuring/setting range		
Measuring range	[bar]	0...100
Accuracy / deviations		
Repeatability		< 0,1; (with temperature fluctuations < 10 K)
[% of the final value]		
Characteristics deviation		< ± 1,0; (incl. linearity, zero and span error (limit value setting))
[% of the final value]		
Temperature drift per 10 K		< ± 0.3
Reaction times		
Max. response time analog output	[ms]	3
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Material		PA; PBT; stainless steel (1.4404 / 316L)
Materials (wetted parts)		ceramics; PTFE; stainless steel (1.4404 / 316L)
Min. pressure cycles		100 million
Process connection		threaded connection G 1 external thread
Remarks		
Pack quantity		1 pcs.

PL3652



Flush pressure transmitter

PL-100-SEA01-A-ZVG/US/ /P

Electrical connection

Connector: 1 x M12; coding: A



Connection

