


PL5423



Flush pressure transmitter

PL-060-SEG14-A-ZVG/US/ IW



- 1 Gasket DIN 3869-14-FKM
- 2 O-ring 8.5 x 1.5 FKM



Product characteristics			
Number of inputs and outputs	Number of analog outputs: 1		
Measuring range	0...60 bar	0...870 psi	0...6 MPa
Process connection	threaded connection G 1/4 external thread		
Application			
Measuring element	thin film measuring cell with diaphragm seal technique		
Application	Industrial flush pressure transmitters, analog PL; for industrial applications		
Media	viscous media and liquids with suspended particles; liquids and gases		
Medium temperature [°C]	-20...90		
Min. bursting pressure	900 bar	13050 psi	90 MPa
Pressure rating	150 bar	2175 psi	15 MPa
Note on pressure rating	static		
Vacuum resistance [mbar]	-1000		
Type of pressure	relative pressure		



Flush pressure transmitter

PL-060-SEG14-A-ZVG/US/ IW

Electrical data			
Operating voltage	[V]	8.5...36 DC	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Protection class		III	
Reverse polarity protection		yes	
Power-on delay time	[s]	0.1	
Inputs / outputs			
Number of inputs and outputs		Number of analog outputs: 1	
Outputs			
Total number of outputs		1	
Output signal		analog signal	
Number of analog outputs		1	
Analog current output	[mA]	4...20	
Max. load	[Ω]	(Ub – 8,5 V) / 21,5 mA; @8,5V= 0 Ω; @12V max. 160 Ω; @24V max. 720 Ω	
Short-circuit proof		yes	
Overload protection		yes	
Measuring/setting range			
Measuring range		0...60 bar	0...870 psi 0...6 MPa
Accuracy / deviations			
Repeatability	[% of the span]	< ± 0,05; (with temperature fluctuations < 10 K)	
Characteristics deviation	[% of the span]	< ± 0,5; (incl. drift when overtightened, zero point and span error, non-linearity, hysteresis)	
Linearity deviation	[% of the span]	< ± 0,1 (BFSL) / < ± 0,2 (LS)	
Hysteresis deviation	[% of the span]	< ± 0,2	
Long-term stability	[% of the span]	< ± 0,1; (per 6 months)	
Temperature coefficient zero point	[% of the span / 10 K]	< 0,35 (-25...90 °C)	
Temperature coefficient span	[% of the span / 10 K]	< 0,15 (-25...90 °C)	
Reaction times			
Step response time analog output	[ms]	2	
Operating conditions			
Ambient temperature	[°C]	-25...90	
Storage temperature	[°C]	-25...100	
Protection		IP 67; IP 69K	
Tests / approvals			
EMC		DIN EN 61000-6-2	
		DIN EN 61000-6-3	
Shock resistance		DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	20 g (10...2000 Hz)

PL5423



Flush pressure transmitter

PL-060-SEG14-A-ZVG/US/ IW

MTTF	[years]	787
UL approval	UL approval number	J045
	File number UL	E174189

Mechanical data		
Weight	[g]	65
Material	stainless steel (630/1.4542/17-4 PH); stainless steel (1.4404 / 316L); PEI	
Materials (wetted parts)	stainless steel (630/1.4542/17-4 PH); stainless steel (1.4435 / 316L); FKM	
Min. pressure cycles	60 million; (at 1.2 times nominal pressure)	
Tightening torque	[Nm]	25...35; (recommended tightening torque; Depends on lubrication, seal and pressure rating)
Process connection	threaded connection G 1/4 external thread	
Process connection sealing	FKM	
Fill fluid for pressure transfer	NEOBEE (food grade, FDA compliant)	

Accessories		
Items supplied	O-ring : 8,5mm x 1,5mm, FKM, E30517	
	Gasket : G1/4 DIN EN ISO 1179-2, FKM, E30145	
Accessories (optional)	O-ring : 5 x (8,5mm x 1,5 mm), FKM, E30517	
	O-ring : 1 x (8,5mm x 1,5 mm), FFKM, E30518	
	O-ring : 5 x (8,5mm x 1,5 mm), EPDM, E30519	
	Gasket : 10 x G/1/4 DIN EN ISO 1179-2, FKM, E30145	
	Gasket : 1 x G/1/4 DIN EN ISO 1179-2, FFKM, E30520	
	Gasket : 10 x G/1/4 DIN EN ISO 1179-2, EPDM, E30442	

Remarks		
Remarks	BFSL = Best Fit Straight Line	
	LS = limit value setting	
Pack quantity	1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A




PL5423



Flush pressure transmitter

PL-060-SEG14-A-ZVG/US/ IW

Connection



OUT	analog output Colors to DIN EN 60947-5-2 Core colors :
BN	brown
WH	white