




Retro-reflective sensor

OUP-HNKG/6M

Article no longer available - archive entry



Receiver in upper lens
transmitter in lower lens



Product characteristics

Type of light	red light
Housing	rectangular

Application

System	polarization filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	< 30
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		NPN
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	160
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes

Monitoring range

Range	[m]	< 1.5; (Prismatic reflector Ø 80 E20005)
Range adjustable		yes
Polarization filter available		yes



OU5095



Retro-reflective sensor

OUP-HNKG/6M

Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		rectangular
Dimensions	[mm]	28 x 16 x 51
Material		PPO modified
Lens material		glass
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied		Angle bracket
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 6 m; 3 x 0.34 mm²		
Connection		



Core colors :
BK = black
BN = brown
BU = blue