

PB5324




Pressure sensor with LED bar display

PB-010PRBU76-HFPKG/US/ IV

Article no longer available - archive entry

Alternative articles: PN7304
When selecting an alternative article and accessories please note that technical data may differ!



| Product characteristics | | |
|------------------------------|-------|--|
| Number of inputs and outputs | | Number of digital outputs: 1 |
| Measuring range | [psi] | 0...100 |
| Process connection | | threaded connection 7/16" - 20 UNF Internal thread |
| Application | | |
| System | | gold-plated contacts |
| Application | | for industrial applications |
| Media | | liquids and gases |
| Medium temperature | [°C] | -25...80 |
| Min. bursting pressure | [psi] | 2000 |
| Pressure rating | [psi] | 700 |
| Type of pressure | | relative pressure |
| Electrical data | | |
| Operating voltage | [V] | 18...30 DC |
| Current consumption | [mA] | 50 |
| Min. insulation resistance | [MΩ] | 100; (500 V DC) |
| Protection class | | III |
| Reverse polarity protection | | yes |



Pressure sensor with LED bar display

PB-010PRBU76-HFPKG/US/ IV

| | | |
|---|---------------------------|--|
| Power-on delay time | [s] | 0.2 |
| Integrated watchdog | | yes |
| Inputs / outputs | | |
| Number of inputs and outputs | | Number of digital outputs: 1 |
| Outputs | | |
| Total number of outputs | | 1 |
| Output signal | | switching signal |
| Electrical design | | PNP |
| Number of digital outputs | | 1 |
| Output function | | normally open / closed; (configurable) |
| Max. voltage drop switching output DC | [V] | 2 |
| Permanent current rating of switching output DC | [mA] | 250 |
| Switching frequency DC | [Hz] | 10 |
| Short-circuit protection | | yes |
| Type of short-circuit protection | | yes (non-latching) |
| Overload protection | | yes |
| Measuring/setting range | | |
| Measuring range | [psi] | 0...100 |
| Set point SP | [psi] | 5...100 |
| Reset point rP | [psi] | 3...98 |
| In steps of | [psi] | 1 |
| Note on hysteresis | | adjustable |
| Accuracy / deviations | | |
| Switch point accuracy | [% of the final value] | < ± 2,0 |
| Repeatability | | |
| | [% of the final value] | < ± 0,25; (with temperature fluctuations < 10 K) |
| Temperature drift per 10 K | | < ± 0.3 |
| Software / programming | | |
| Adjustment of the switch point | | Programming button |
| Operating conditions | | |
| Ambient temperature | [°C] | -25...80 |
| Storage temperature | [°C] | -40...100 |
| Protection | | IP 65 |
| Tests / approvals | | |
| EMC | EN 61000-4-2 ESD | 4 kV CD / 8 kV AD |
| | EN 61000-4-3 HF radiated | 10 V/m |
| | EN 61000-4-4 Burst | 2 kV |
| | EN 61000-4-6 HF conducted | 10 V |
| Shock resistance | DIN IEC 68-2-27 | 50 g (11 ms) |
| Vibration resistance | DIN IEC 68-2-6 | 20 g (10...2000 Hz) |

PB5324



Pressure sensor with LED bar display

PB-010PRBU76-HFPKG/US/ IV

| Mechanical data | | |
|--------------------------|---|--|
| Material | EPDM/X; FKM; NBR; PA; PBT; PC; PTFE; stainless steel (1.4301 / 304) | |
| Materials (wetted parts) | FKM; ceramics; stainless steel (1.4305 / 303) | |
| Min. pressure cycles | 100 million | |
| Process connection | threaded connection 7/16" - 20 UNF Internal thread | |

| Displays / operating elements | | |
|-------------------------------|------------------|--|
| Display | Switching status | LED, yellow |
| | Measured values | 10 x LED, green Resolution 10 % of the final value |

| Remarks | |
|---------------|--------|
| Pack quantity | 1 pcs. |

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated

