




## Pressure transmitter with ceramic measuring cell

PD-025-SBN14-A-ZVG/US/ /E

Article no longer available - archive entry



### Product characteristics

Number of inputs and outputs	Number of analog outputs: 1
Measuring range [bar]	0...25
Process connection	threaded connection 1/4" NPT external thread

### Application

System	gold-plated contacts
Application	for industrial applications
Media	liquids and gases
Cannot be used for	oils
Medium temperature [°C]	-25...90; (on request: -40...90 °C)
Min. bursting pressure [bar]	350
Pressure rating [bar]	150
Type of pressure	relative pressure

### Electrical data

Operating voltage [V]	9.6...32 DC
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes

### Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 1
------------------------------	-----------------------------

### Outputs

Total number of outputs	1
-------------------------	---



## Pressure transmitter with ceramic measuring cell

PD-025-SBN14-A-ZVG/US/ /E

Output signal	analog signal	
Number of analog outputs	1	
Analog current output [mA]	4...20	
Max. load [Ω]	720; (Ub = 24 V; (Ub - 9,6 V) / 20 mA)	
Overload protection	yes	
Measuring/setting range		
Measuring range [bar]	0...25	
Accuracy / deviations		
Repeatability [% of the span]	< 0,1; (with temperature fluctuations < 10 K)	
Characteristics deviation [% of the span]	< ± 0,5; (BFSL = Best Fit Straight Line; LS = limit value setting)	
Long-term stability [% of the span]	< ± 0,05; (per 6 months)	
Temperature coefficient zero point [% of the span / 10 K]	0,1; (-25...80 °C)	
Temperature coefficient span [% of the span / 10 K]	0,2; (-25...80 °C)	
Reaction times		
Step response time analog output [ms]	3	
Operating conditions		
Ambient temperature [°C]	-25...80	
Storage temperature [°C]	-40...100	
Protection	IP 65	
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	30 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Weight [g]	219.4	
Material	stainless steel (1.4404 / 316L); FKM; PA; EPDM/X	
Materials (wetted parts)	stainless steel (1.4305 / 303); ceramics; EPDM/X	
Min. pressure cycles	100 million	
Process connection	threaded connection 1/4" NPT external thread	
Remarks		
Pack quantity	1 pcs.	

# PD3223



## Pressure transmitter with ceramic measuring cell

PD-025-SBN14-A-ZVG/US/ /E

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection

