

PN7224




Pressure sensor with display

PN-015PRBN14-QFPKG/US/ IV

Article no longer available - archive entry

Alternative articles: PN7204
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics		
Number of inputs and outputs		Number of digital outputs: 2
Measuring range	[psi]	0...150
Process connection		threaded connection 1/4" NPT external thread
Application		
System		gold-plated contacts
Application		for industrial applications
Media		liquids and gases
Medium temperature	[°C]	-25...80
Min. bursting pressure	[psi]	2000
Pressure rating	[psi]	700
Type of pressure		relative pressure
Electrical data		
Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 60
Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes

PN7224



Pressure sensor with display

PN-015PRBN14-QFPKG/US/ IV

Power-on delay time	[s]	0.2
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2
Outputs		
Total number of outputs		2
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		2
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Measuring/setting range		
Measuring range	[psi]	0...150
Set point SP	[psi]	3...150
Reset point rP	[psi]	1...148
In steps of	[psi]	2
Accuracy / deviations		
Switch point accuracy	[% of the final value]	$< \pm 1,0$
Repeatability	[% of the final value]	$< \pm 0,25$; (with temperature fluctuations < 10 K)
Temperature drift per 10 K		$< \pm 0.3$
Reaction times		
Switching frequency for a given set response time of one output	Response time (dAP)	3 6 10 17 30 60 125 250 500
	Switching frequency	170 80 50 30 16 8 4 2 1
Response time	[ms]	at rectangular pressure characteristic; Set point (SPx) = 70 %; Reset point (rPx) = 30 %
Delay time programmable dS, dr	[s]	0, 0,2,...10, 11,...50
Software / programming		
Adjustment of the switch point		Programming button
Parameter setting options		hysteresis / window; normally open / closed; switch-on/switch-off delay; Damping
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 65

PN7224



Pressure sensor with display

PN-015PRBN14-QFPKG/US/ IV

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
Mechanical data		
Material	EPDM/X; FKM; PA; PBT; PC; PTFE; stainless steel (1.4301 / 304)	
Materials (wetted parts)	stainless steel (1.4305 / 303); ceramics; FKM	
Min. pressure cycles	100 million	
Process connection	threaded connection 1/4" NPT external thread	
Displays / operating elements		
Display	Switching status	2 x LED, red
	Function display	7-segment LED display
	Measured values	7-segment LED display
Remarks		
Pack quantity	1 pcs.	
Electrical connection		

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

