
PS3417

Hydrostatic submersible pressure transmitter

SUBMERSIBLE 1BAR 15M PUR CABLE





C€ CA

Product characteristics						
Number of inputs and outputs		Number of analog outputs: 1				
Measuring range	0	01 bar	01000 mba	o14.5 psi	0401.5 inH2O	0100 kPa
Application						
Design		with capillary tube for pressure compensation				
Application		for industrial applications				
Media		Liquids				
Medium temperature	[°C]	-1050				
Min. bursting pressure	6	6 bar	8	37 psi	600 kPa	
Pressure rating	5	5 bar	7	'2.5 psi	500 kPa	
Type of pressure		relative pressure				
Electrical data						
Operating voltage	[V]	1030 DC				
Protection class		III				
Reverse polarity protection				yes		
Measuring principle		hydrostatic				
Inputs / outputs						
Number of inputs and outputs		Number of analog outputs: 1				
Outputs						
Total number of outputs				1		
Output signal		analog signal				
Number of analog outputs		1				
Analog current output [r	mA]			420		
Max. load	[Ω]		700;	(Ub = 24 V; (Ub - 10	0 V) / 20 mA)	
Short-circuit protection				yes		
Measuring/setting range						
Measuring range	0	01 bar	01000 mba	r 014.5 psi	0401.5 inH2O	0100 kPa
Accuracy / deviations						
Repeatability [% of the sp	an]		< 0,1; (with temperature fluc	tuations < 10 K)	
Characteristics deviation [% of the sp	oan]	< 0,5 (BFSL) /1; (incl. linearity, zero and span error (limit value setting))				
Linearity deviation [% of the sp	oan]	< 0,2 (BFSL)				
Long-term stability [% of the sp	oan]			< 0,2; (per yea	ar)	

PS3417

Hydrostatic submersible pressure transmitter




SUBMERSIBLE 1BAR 15M PUR CABLE

Temperature coefficient zero point [% of the span / 10 K]		< ± 0,2; (050 °C)		
Temperature coefficient span [% of the span / 10 K]		< ± 0,2; (050 °C)		
Operating conditions				
Ambient temperature	[°C]	-1050		
Storage temperature	[°C]	-3080		
Protection		IP 68		
Tests / approvals				
MTTF	[years]	403		
Pressure equipment directive		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request		
Mechanical data				
Weight	[g]	1284.55		
Material		stainless steel (1.4571/316Ti); PA		
Remarks				
Pack quantity		1 pcs.		
Electrical connection				

Electrical connection

Cable: 15 m, PUR, Ø 7.5 mm; Core insulation:, PVC

Connection



Core colors :

BN = brown GY = greyWH = white