
PS4208

Hydrostatic submersible pressure transmitter

SUBMERSIBLE 0,25BAR 5M FEP CABLE





C€ CA

Product characteri	stics					
Number of inputs ar			Nι	umber of analog ou	utputs: 1	
Measuring range		00.25 bar	0250 mbar	03.63 psi	0100.4 inH2O	025 kPa
Application						
Design			with capilla	ary tube for pressu	re compensation	
Application				for industrial applic	cations	
Media				Liquids		
Medium temperatur	e [°C]			-1085		
Min. bursting pressu	ıre	2.4 bar	35	psi	240 kPa	
Pressure rating		2 bar	29	psi	200 kPa	
Type of pressure				relative pressu	ire	
Electrical data						
Operating voltage	[V]			1030 DC		
Protection class		III				
Reverse polarity pro	otection	yes				
Measuring principle		hydrostatic				
Inputs / outputs						
Number of inputs ar	nd outputs	Number of analog outputs: 1				
Outputs						
Total number of outp	outs			1		
Output signal		analog signal				
Number of analog o	utputs	1				
Analog current outp	ut [mA]	420				
Max. load	[Ω]		700; (Ub = 24 V; (Ub - 10	0 V) / 20 mA)	
Short-circuit protect	ion			yes		
Measuring/setting	range					
Measuring range		00.25 bar	0250 mbar	03.63 psi	0100.4 inH2O	025 kPa
Accuracy / deviation	ons					
Repeatability	[% of the span]		< 0,1; (wit	th temperature fluc	ctuations < 10 K)	
Characteristics devi	ation [% of the span]	< 0,25	(BFSL) / 0,5; (incl.	. linearity, zero and	l span error (limit valu	ue setting))
Linearity deviation	[% of the span]	< 0,2 (BFSL)				
Long-term stability	[% of the span]			< 0,2; (per yea	ar)	

PS4208

Hydrostatic submersible pressure transmitter



SUBMERSIBLE 0,25BAR 5M FEP CABLE

Temperature coefficient zero point [% of the span / 10 K]	< ± 0,2; (050 °C)
Temperature coefficient span [% of the span / 10 K]	< ± 0,2; (050 °C)

Operating conditions		
Ambient temperature	[°C]	-1085
Storage temperature	[°C]	-3080
Protection		IP 68

Tests / approvals			
MTTF	[years]	403	
Pressure equipment directive		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			


Mechanical data			
Weight	[g]	650.6	
Material		stainless steel (1.4571/316Ti); PA	
Domorko			

Remarks	
Pack quantity	1 pcs.

Electrical connection

Cable: 5 m, FEP, Ø 7.5 mm

Connection



1: screen (connected to the housing)

Core colors:

BN = brown GN = green