

PU504E



Pressure transmitter

PU-010-SEG14-C-DVG/US



1 sealing



Product characteristics

Number of inputs and outputs	Number of analog outputs: 1			
Measuring range	0...10 bar	0...145 psi	0...1000 kPa	0...1 MPa
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)			

Application

Application	for mobile applications		
Media	liquids and gases		
Medium temperature [°C]	-40...125		
Min. bursting pressure	300 bar	4350 psi	30 MPa
Pressure rating	25 bar	360 psi	2.5 MPa
Note on pressure rating	static		
Vacuum resistance [mbar]	-1000		
Type of pressure	relative pressure		

Electrical data

Operating voltage [V]	8...32 DC
Current consumption [mA]	< 12
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	< 0.1

Inputs / outputs

Number of inputs and outputs	Number of analog outputs: 1
------------------------------	-----------------------------

Outputs

Total number of outputs	1
Output signal	analog signal
Number of analog outputs	1
Analog voltage output [V]	0.5...4.5

PU504E



Pressure transmitter

PU-010-SEG14-C-DVG/US

Min. load resistance	[Ω]	2000			
Short-circuit proof		yes			
Overload protection		yes			
Measuring/setting range					
Measuring range		0...10 bar	0...145 psi	0...1000 kPa	0...1 MPa
Accuracy / deviations					
Repeatability	[% of the span]	< ± 0,05; (with temperature fluctuations < 10 K)			
Characteristics deviation	[% of the span]	< ± 0,8; (incl. drift when overtightened, zero point and span error, non-linearity, hysteresis)			
Linearity deviation	[% of the span]	< ± 0,25 (BFSL) / < ± 0,5 (LS)			
Hysteresis deviation	[% of the span]	< ± 0,2			
Long-term stability	[% of the span]	< ± 0,1; (per 6 months)			
Temperature coefficient zero point	[% of the span / 10 K]	< ± 0,1 (0...80 °C); < ± 0,2 (-40...0 °C / 80...125 °C)			
Temperature coefficient span	[% of the span / 10 K]	< ± 0,1 (0...80 °C); < ± 0,2 (-40...0 °C / 80...125 °C)			
Reaction times					
Step response time analog output	[ms]	2			
Operating conditions					
Ambient temperature	[°C]	-40...100			
Storage temperature	[°C]	-40...100			
Protection		IP 67; IP 69K			
Tests / approvals					
EMC		compliant with UN ECE R10, rev. 5			
		ISO 11452-2		100 V/m	
		DIN EN 61326-1			
Shock resistance		DIN EN 60068-2-27		500 g (1 ms)	
Vibration resistance		DIN EN 60068-2-6		20 g (10...2000 Hz)	
MTTF	[years]	658			
Pressure equipment directive		sound engineering practice; can be used for group 2 fluids; group 1 fluids on request			
Mechanical data					
Weight	[g]	58.4			
Material		stainless steel (630/1.4542/17-4 PH); stainless steel (1.4404 / 316L); PEI			
Materials (wetted parts)		stainless steel (630/1.4542/17-4 PH)			
Min. pressure cycles		60 million; (at 1.2 times nominal pressure)			
Tightening torque	[Nm]	25...35; (recommended tightening torque; Depends on lubrication, seal and pressure rating)			
Process connection		threaded connection G 1/4 external thread (DIN EN ISO 1179-2)			
Process connection sealing		HNBR (DIN EN ISO 1179-2)			
Restrictor element integrated		yes			

PU504E



Pressure transmitter

PU-010-SEG14-C-DVG/US


Remarks	
Remarks	BFSL = Best Fit Straight Line
	LS = limit value setting
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Maximum cable length: 30 m



Connection



OUT analog output
 Colors to DIN EN 60947-5-2
 Core colors :
BN = brown
BU = blue
WH = white