

PM2666




Flush pressure transmitter

PM-2,5-REA01-E-ZVG/US/ /P

Article no longer available - archive entry

Alternative articles: PM2656
When selecting an alternative article and accessories please note that technical data may differ!



- 1 Tightening torque 20 Nm
- 2 diaphragm : PTFE



Product characteristics			
Number of inputs and outputs	Number of analog outputs: 1		
Measuring range	-0.13...2.5 bar	-1.8...36.3 psi	-13...250 kPa
Process connection	threaded connection G 1 external thread		
Application			
Application	flush mountable for the food and beverage industry		
Media	liquid and viscous media		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	50 bar	725 psi	5000 kPa
Pressure rating	20 bar	290 psi	2000 kPa
Type of pressure	relative pressure		
No dead space	yes		



Flush pressure transmitter

PM-2,5-REA01-E-ZVG/US/ /P

Electrical data			
Operating voltage	[V]	14...30 DC; (cULus - Class 2 source required)	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Protection class		III	
Reverse polarity protection		yes	
Inputs / outputs			
Number of inputs and outputs		Number of analog outputs: 1	
Outputs			
Total number of outputs		1	
Output signal		analog signal	
Number of analog outputs		1	
Analog current output	[mA]	4...20	
Max. load	[Ω]	550; (Ub = 24 V; (Ub - 13 V) / 20 mA)	
Overload protection		yes	
Measuring/setting range			
Measuring range		-0.13...2.5 bar	-1.8...36.3 psi -13...250 kPa
Analog start point		-0.13...1.88 bar	-1.8...27.2 psi -13...188 kPa
Analog end point		0.5...2.5 bar	7.3...36.3 psi 50...250 kPa
In steps of		0.01 bar	0.1 psi 1 kPa
Accuracy / deviations			
Repeatability	[% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)	
Characteristics deviation	[% of the span]	< ± 0,6; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)	
Linearity deviation	[% of the span]	< ± 0,5; (Turn down 1:1)	
Hysteresis deviation	[% of the span]	< ± 0,1; (Turn down 1:1)	
Long-term stability	[% of the span]	< ± 0,1; (Turn down 1:1; per year)	
Temperature coefficient zero point	[% of the span / 10 K]	< ± 0,15; (0...80 °C)	
Temperature coefficient span	[% of the span / 10 K]	< ± 0,4; (0...80 °C)	
Reaction times			
Max. response time analog output	[ms]	3	
Software / programming			
Parameter setting options		Zero point; span	
Interfaces			
Communication interface		EPS	
Operating conditions			
Ambient temperature	[°C]	-25...80	
Storage temperature	[°C]	-40...100	
Protection		IP 67	

PM2666



Flush pressure transmitter

PM-2,5-REA01-E-ZVG/US/ /P

Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

Mechanical data	
Material	stainless steel (1.4404 / 316L); PA; PBT
Materials (wetted parts)	stainless steel (1.4435 / 316L); PTFE on ceramic substrate; PTFE
Min. pressure cycles	100 million
Process connection	threaded connection G 1 external thread

Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A



Connection

