

PM2054




Flush pressure transmitter

PM-010-RES30-E-ZVG/US/ /P

Article to be discontinued
Discontinuation date: 03/31/2024

Alternative articles: PI1004 or PM1704
When selecting an alternative article and accessories please note that technical data may differ!

Please do not use for new projects.
no more adapters available as accessories



- 1 Aseptoflex sealing edge
- 2 Aseptoflex thread



Product characteristics

Number of inputs and outputs	Number of analog outputs: 1			
Measuring range	-0.5...10 bar	-7...145 psi	-50...1000 kPa	-0.05...1 MPa
Process connection	threaded connection Aseptoflex external thread Aseptoflex			

Application

System	gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Media	viscous media and liquids with suspended particles; liquids and gases		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	150 bar	2175 psi	15000 kPa
Pressure rating	50 bar	725 psi	5000 kPa



Flush pressure transmitter

PM-010-RES30-E-ZVG/US/ /P

Type of pressure	relative pressure			
No dead space	yes			
Electrical data				
Operating voltage [V]	14...30 DC			
Min. insulation resistance [MΩ]	100; (500 V DC)			
Protection class	III			
Reverse polarity protection	yes			
Inputs / outputs				
Number of inputs and outputs	Number of analog outputs: 1			
Outputs				
Total number of outputs	1			
Output signal	analog signal			
Number of analog outputs	1			
Analog current output [mA]	4...20			
Max. load [Ω]	550; (U _b = 24 V; (U _b - 13 V) / 20 mA)			
Overload protection	yes			
Measuring/setting range				
Measuring range	-0.5...10 bar	-7...145 psi	-50...1000 kPa	-0.05...1 MPa
Analog start point	-0.5...7.49 bar	-7...109 psi	-50...749 kPa	
Analog end point	2...9.99 bar	29...145 psi	200...999 kPa	
In steps of	0.01 bar	1 psi	1 kPa	
Factory setting		ASP = 0.00 bar	AEP = 9.99 bar	
Accuracy / deviations				
Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)			
Characteristics deviation [% of the span]	< ± 0,6; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)			
Linearity deviation [% of the span]	< ± 0,5; (Turn down 1:1)			
Hysteresis deviation [% of the span]	< ± 0,1; (Turn down 1:1)			
Long-term stability [% of the span]	< ± 0,1; (Turn down 1:1; per year)			
Temperature coefficient zero point [% of the span / 10 K]	< ± 0,1; (0...80 °C)			
Temperature coefficient span [% of the span / 10 K]	< ± 0,2; (0...80 °C)			
Reaction times				
Max. response time analog output [ms]	3			
Software / programming				
Parameter setting options	Zero point; span			
Interfaces				
Communication interface	EPS			

PM2054



Flush pressure transmitter

PM-010-RES30-E-ZVG/US/ /P

Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	1 GHz / Accuracy < 2,5%
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]	271
Mechanical data		
Weight	[g]	474.5
Material		stainless steel (1.4404 / 316L); PEI; FKM
Materials (wetted parts)		ceramics (99.9 % Al2O3); stainless steel (1.4404 / 316L); surface characteristics: Ra < 0,4 / Rz 4; PTFE
Min. pressure cycles		100 million
Process connection		threaded connection Aseptoflex external thread Aseptoflex
Remarks		
Remarks		The 3-A qualification is only valid if adapters with 3-A qualification are used for installation.
Notes		Please do not use for new projects.; no more adapters available as accessories
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: gold-plated		
Connection		

