
PX3524

Pressure transmitter with ceramic measuring cell

PA-1-10RBG14-A-ZVG/US/ /V







Product characteristics					
Number of inputs and outputs		Number of analog outputs: 1			
Measuring range	[bar]	-110			
Process connection		threaded connection G 1/4 external thread Internal thread:M5			
Application					
System		gold-plated contacts			
Application		for industrial applications			
Media		liquids and gases			
Medium temperature	[°C]	-2590; (on request: -4090 °C)			
Min. bursting pressure	[bar]	150			
Pressure rating	[bar]	75			
Type of pressure		relative pressure; vacuum			
Electrical data					
Operating voltage	[V]	9.632 DC			
Min. insulation resistance	$[M\Omega]$	100; (500 V DC)			
Protection class		III			
Reverse polarity protection		yes			
Inputs / outputs					
Number of inputs and outputs		Number of analog outputs: 1			
Outputs					
Total number of outputs		1			
Output signal		analog signal			
Number of analog outputs		1			

PX3524

Pressure transmitter with ceramic measuring cell



PA-1-10RBG14-A-ZVG/US/ /V

Analog current output	[mA]		420	
Max. load	[Ω]	720; (Ub = 24 V; (Ub - 9,6 V) / 20 mA)		
Overload protection			yes	
Measuring/setting range				
Measuring range	[bar]		-110	
Accuracy / deviations				
· ·	he span]	< 0,1; (with t	temperature fluctuations < 10 K)	
Characteristics deviation [% of the span]		$< \pm 0.25$ (BFSL) $/ < \pm 0.5$ (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)		
Long-term stability [% of the span]		< ± 0,05; (per 6 months)		
Temperature coefficient zero point		0,1; (080 °C)		
[% of the span / 10 K]				
Temperature coefficient span [% of the span / 10 K]		0,2; (080 °C)		
Reaction times				
Step response time analog output	[ms]		3	
Operating conditions				
Ambient temperature	[°C]		-2580	
Storage temperature	[°C]	-40100		
Protection			IP 65	
Tests / approvals				
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD	
		EN 61000-4-3 HF radiated	30 V/m	
		EN 61000-4-4 Burst	2 kV	
		EN 61000-4-6 HF conducted	10 V	
		radiation of interference	according to the automotive directive 2004/104/EC / CISPR 25	
		noise immunity	according to the automotive directive 2004/104/EC / ISO 11452-2	
		HF radiated	100 V/m	
		pulse resistance	ISO 7637-2 / severity level 3	
Shock resistance		DIN IEC 68-2-27	50 g (11 ms)	
Vibration resistance		DIN IEC 68-2-6	20 g (102000 Hz)	
MTTF	[years]		555	
Pressure equipment directive		sound engineering practice; can	be used for group 2 fluids; group 1 fluids on request	
Mechanical data				
Weight	[g]		218	
Material		stainless steel (1.4404 / 316L); FKM; PA; EPDM/X		
Materials (wetted parts)		stainless steel (1.4305 / 303); ceramics; sealing: FKM DIN 3869-14		
Min. pressure cycles		100 million		
Process connection		threaded connection G 1/4 external thread Internal thread:M5		
Restrictor element integrated		no (can be retrofitted)		

PX3524

Connection

Pressure transmitter with ceramic measuring cell



PA-1-10RBG14-A-ZVG/US/ /V

Remarks			
Pack quantity	1 pcs.		
Electrical connection			
Connector: 1 x M12; coding: A; Contacts: gold-plated			
3 4			

